
LAMP

MonoFlat LIN-X hinge ®

MonoFlat LIN-X 450 Standard kit Instruction Manual

Thank you for purchasing this MonoFlat LIN-X hinge by SUGATSUNE. Before proceeding with the installation, please read this instruction manual carefully for the best possible result and ensure your safety.




WARNING

- Failure to observe the following precautions may result in injury and/or lead to damage to surrounding cabinets or fittings.
- Choose suitable screws to ensure of proper installation of the cabinet and door.
- Ensure that door size, weight and material correspond to the specifications stated in this manual.
- Do not disassemble or modify the system.

■ Product Specification


The state of the s	
Door width	400 - 500 mm
Door height	600 - 900 mm
Door thickness	15 - 24 mm
Door weight	Max 7 kg (per door)

Parts List




■Overall (unit: mm)

Picture shows the left hand door use. (Right hand door use is symmetrical.)




■Overlay distance


- Side overlay as shown in Fig.1 is: 19 mm for mounting plate 230-P4W-32T 14 mm for mounting plate 230-P4W-32T+5
- An opening clearance of 2 mm is required on both sides of the door.



■Position of LIN-X Body


• Prepare the door as per Fig.2 and Fig.3





■Mounting Plate Position


• Prepare the sideboard for mounting plate installation as Fig.4






■Installation


1 Mounting plate installation:




2 Cup Cover installation:




Ensure that the two O are pointing toward the edge of the door.






⑦ Binding & tapping screw3.5×15

Ensure that the two LIN-X bodies are parallel by measuring both the base and mounting plate distances.





5 Door installation:



Ensure that the LIN-X body is securely attached to the mounting plates.

Adjustments





SUGATSUNE KOGYO CO.,LTD

Tokyo, JAPANPhone: +81 (0)3 3866 2260 E-mail:export@sugatsune.co.jp

SUGATSUNE KOGYO (UK) LTD

Reading, UK
Phone: +44 118 9272 955 E-mail:sales@sugatsune.co.uk

SUGATSUNE EUROPE GmbH

ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center) certified

Düsseldorf, GERMANY Phone: +49 211 53812900 E-mail:sales@sugatsune.eu

SUGATSUNE SHANGHAI Co., LTD

Shanghai, CHINA Phone: +86 21 3632 1858

E-mail:lamp@sugatsune.com.cn

Guangzhou, CHINA Phone: +86 20 6639 3552

E-mail:lamp@sugatsune.com.cn

SUGATSUNE KOGYO INDIA PRIVATE LIMITED

Mumbai, INDIA
Phone: +91 22 28314490/91 E-mail:sales@sugatsune.in

SUGATSUNE AMERICA, INC

Chicago, USA
Phone: +1 630 317 7072 E-mail:sales@sugatsune.com

SUGATSUNE CANADA, INC.
Phone: +1 514 312 5267 E-mail:support@sugatsune.ca