

Dear Customer:

The SLS-ELAN stay was designed and manufactured with Sugatsune utmost care in order to give you a high performance and smooth operation on a long-term basis. We ask you to follow these instructions for best possible results and carefree use throughout its lifetime.

Safety recommendations:

- Sugatsune recommends for the installation to be made by a professional carpenter or installer.
- The SLS-ELAN stay contains some very strong springs: for your own safety, do not fold
 the arm before it is securely attached to the door. Failure to observe this advice may
 lead to bodily injury.
- · Do not disassemble the arm or body of the stay.
- · Please use this stay only within the specifications indicated below.
- · Standard temperature of use is 0 to 40°C.

Warranty

- Do not pull the arm down without door attached as it will spring back up violently and may cause serious injuries.
- The SLS-ELAN stay was produced with a particular attention to its quality. Should you however experience any difficulty, please refer to your local supplier or the Sugatsune export department (export@sugatsune.co.jp).
- The liability of Sugatsune is limited to the replacement or repair of the stay itself.
 Sugatsune cannot accept any liability for damaged incurred while using this stay.
- · Standard guaranty is for a one-year period from the date of shipment.

Specifications

SLS-ELAN specifications are applicable in the list below.
For dimensions other than mentioned below, select the type based on the calculation below.


SLS-ELAN-HL(R)

SLS-ELAN-ML(R)

**The following table provides an overview of the possible door sizes for which SLS-ELAN can be used.

It is given on an indicative basis only and does not constitute a guaranty in itself. Please always test assembly.

*Torque shown for 1 stay.
Double if used in pairs.




Calculation method


 $\frac{\text{Door height(m)}}{2} \times \underset{\text{including handle(kg)}}{\text{Weight of door}} \times 9.8 = \underset{(N \cdot m)}{\text{Lifting Power}}$

4.9~7.35N·m(50~75kgf·cm): SLS-ELAN-ML(R) 7.35~9.8N·m(75~100kgf·cm): SLS-ELAN-HL(R)


Set content




Installation drawing




Installation







3 Door installation




<u>Do not pull the arm down without door attached as it will spring back up violently and may cause serious injuries.</u>

4 Mounting plate and arm attachment






·Insert the pin of the mounting plate in the Slider




·Attach the Slider with the fixing bolt M4x5

·Line up the Slider with the pin of the mounting plate

5 Final adjustment






·If you feel that the door is too light (self lift-up) or too heavy (self-closing), it is possible to limit the action of the spring by tightening the adjustment screw.


⚠ When using a light door, an under-tightened adjustment screw may result in a fast opening of the door.

⚠ Do not over-tighten the adjustment screw as this may damage the Slider.

6 Cover assembly and removal



Fix the front of the cover and then clip the back in place.



To remove cover, pull the back side first.

SUGATSUNE AMERICA, INC

SUGATSUNE KOGYO CO.,LTD

Tokyo, JAPAN
Phone: +81 (0)3 3866 2260 E-mail:export@sugatsune.co.jp SUGATSUNE KOGYO (UK) LTD

SUGATSUNE EUROPE GmbH

Düsseldorf, GERMANY Phone: +49 211 53812900 E-mail:sales@sugatsune.eu ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

SUGATSUNE SHANGHAI Co., LTD

Shanghai, CHINA Phone: +86 21 3632 1858 E-mail:lamp@sugatsune.com.cn

Guangzhou, CHINA E-mail:lamp@sugatsune.com.cn Phone: +86 20 6639 3552

SUGATSUNE KOGYO INDIA PRIVATE LIMITED Mumbai, INDIA

Phone: +91 22 28314490/91 E-mail:sales@sugatsune.in

Chicago, USA

SUGATSUNE CANADA, INC. Phone: +1 514 312 5267 E-mail:support@sugatsune.ca

Phone: +1 312 461 1081 E-mail:chicagoshowroom@sugatsune.com.

2017 05 0447-4