



- ⚠ Always adjust the left & right opening angle simultaneously.
- \triangle Do not exceed the adjustment range as it will cause damage to the product.


Check the movement by opening and closing the door after all the adjustments.


Cover installation






Cover removal **Door removal** Mounting plate re-adjustment







Hold the Release lever and move the connecting plate up until it stops.

4

Go to point no. 6 Mounting plate adjustment

SUGATSUNE KOGYO (UK) LTD.

SUGATSUNE EUROPE GmbH

Düsseldorf, GERMANY
Phone: +49 211 53812900 E-mail:sales@sugatsune.eu ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

SUGATSUNE SHANGHAI Co., LTD. Shanghai, CHINA Phone: +86 21 3632 1858 Guangzhou, CHINA Phone: +86 20 6639 3552 E-mail:lamp@sug E-mail:lamp@sugatsune.com.cn E-mail:lamp@sugatsune.com.cn

SUGATSUNE KOREA CO., LTD.
Phone: +82 32 220 0603 F-mail:sales(Phone: +82 32 220 0603 E-mail:sales@sugatsune-korea.co.

SUGATSUNE KOGYO INDIA PRIVATE LIMITED

Mumbai, INDIA
Phone: +04 0967306567

Phone: +91 9867299597 E-mail:sales@sugatsune.in

SUGATSUNE AMERICA, INC.

California, USA
Phone: +1 310 329 6373
Chicago, USA
Phone: +1 630 317 7072
E-mail:sales@sugatsune.com
E-mail:sales@sugatsune.com

SUGATSUNE CANADA, INC.
Phone: +1 514 312 5267 E-mail:support@sugatsune.ca

2023.02 0622-3

LAMP®

HBF-ELAN

Installation instructions

Dear Customer:

HBF-ELAN stay was designed and manufactured with Sugatsune's utmost care in order to give you a high performance and smooth operation on a long-term basis.

We ask you to follow these instructions for best possible results and carefree use throughout its lifetime.

Safety recommendations:

- ·Sugatsune recommends for the installation to be made by a professional carpenter or installer.
- ·HBF-ELAN stay contains some very strong springs: for your own safety, do not fold the arm before
- it is securely attached to the door. Failure to observe this advice may lead to bodily injury.
- ·Do not disassemble the arm or body of the stay.
- ·Please use this stay only within the specifications shown in this manual.
- ·Standard temperature of use is 0 to 40°C.




· Warranty -

·HBF-ELAN stay was produced with a particular attention to its quality.

Should you however experience any difficulty, please refer to your local supplier or Sugatsune Export Department (export@sugatsune.co.jp).

- ·The liability of Sugatsune is limited to the replacement or repair of the stay itself.
- Sugatsune cannot accept any liability for damage incurred while using this stay.
- ·Standard warranty is for one-year period from the date of shipment.

Parts list





■ Body cover

(left): 1 piece



■ Body cover (right): 1 piece



■Mounting plate (left): 1 piece



■ Mounting plate (right): 1 piece



■ Body : 2 pieces

Center hinge 2pieces



■ Body installation screws (3.5x38): 6pieces




(3.5x27): 4pieces

■ Mounting plate installation screws ■ Center hinge installation screws (3.5x15): 12pieces









- Arm installation screws
- Mounting plate installation template

Body installation template

■ Installation instructions · Japanese version: 1 piece, English version(this book): 1 piece

Specifications

- \cdot HBF-ELAN specifications applicable are in the list below. The application range is for information purpose only. We recommend that all installations be tested thoroughly.

	D001 3126						
	Door weight (/door)	2.5~6.5 kg					
	Door height (/door)	320~370mm					
	Door width	MAX 1200mm					
		-					

 Minimum cabinet inside height is 600mm.

* The size of 2 doors should be same.

■ Top door hinge(sold)	separately)specification				
Opening engle	Ourantaur	Tuno			

ı	Opening angle	Overlay	Type
	105° (OLYMPIA hinges recommended)		
1	110°	5~19	Free ewingin
	120°	ا ان	Free swinging
	Single axis hinge	111111	

■ Number of top door hinges requied

е	Door weight	Door width					
E	(/door)	~900mm	901~1200mm				
	2.5~5.5 kg	2pieces	3pieces				
	5.6~6.5 kg	3pieces	3pieces				


■ HBF-ELAN specifications

Door weight (/door)	Item No.				
2.5~3.3 kg	HBF-ELAN-LL				
3.3~4.1 kg	HBF-ELAN-ML				
4.1~4.9 kg	HBF-ELAN-MM				
4.9~5.7 kg	HBF-ELAN-HM				
5.7~6.5 kg	HBF-ELAN-HH				
	2.5~3.3 kg 3.3~4.1 kg 4.1~4.9 kg 4.9~5.7 kg				

- * Select the Door weight range applicable on the list above.
- * Range applicable for a pair of HBF-ELAN.
- * Weight of the door should include the handle.


P.4 P. 1

Installation drawing



Opening dimension

b



120°

134

167

359

351

424

452

120°

120°

	H:Door height											
θ:Top door hinge	320				350			370				
opening angle	а	b	C	θ°	а	b	С	θ°	а	b	С	θ°
105°	58	364	341	105°	65	348	373	105°	69	314	399	105°
110°	85	364	369	110°	93	344	402	110°	99	303	431	110°

148

181

330

313

459

490

120°

120°

157

131

270

289

492

461


(a,b,c:mm)


120°

When using a single axis hinge, adjust the hinge opening angle (θ°) to 120° or less (refer to 7. Door angle adjustment). When using a single axis hinge, please check door operation (movement may vary depending on door mass).


Installation


P.2












- ⚠ Ensure the top door hinges are securely installed so that the door will not drop.
- ⚠ Ensure that all the screws are securely fastened.



P.3