


LAMP**HES**
HIDE • EASY**INSTALLATION MANUAL****FOR HES3D-E190 CONCEALED HINGE**

Thank you for using our product. Before installation, please read this manual thoroughly to ensure correct installation. Please keep this manual at hand for future reference.

ABOUT THE PRODUCT

- This product is a concealed hinge for indoor use that is recessed into door and doorframe.
- Three dimensional adjustment function allows vertical, horizontal, and depth adjustment.
- UL certified - No.R38588

DOOR SPECIFICATION

Min. Door thickness	38 mm
Max. Door weight	100 kg per 2 hinges, 125 kg per 3 hinges
Max. Door size	Width: 900 mm, Height: 2400 mm



COMPONENT PARTS (PER BOX)

• Concealed hinge	2 pcs
• Screw cover	4 pcs × 2 bags
• Template	1 pc
• Countersunk head tapping screw 5×30	8 pcs × 2 bags
• Hex Key 4mm	1 pc

FOR YOUR SAFETY AND CORRECT INSTALLATION**Meaning of symbols**


Caution: If not followed, injury or damage may result.

- ❗ Provide a frame that can withstand the weight and impact of opening and closing the door. Be sure to use the specified screws and tighten them securely. If the mounting strength is insufficient, the door may fall and cause injury.
- ⊘ Do not try to use this product for any other purposes other than originally intended for. Do not use the parts for applications that are out of specification.
- ⊘ Use in conjunction with a door closer is not recommended. For soft-close option, we recommend Sugatsune LDD-V or LDD-S door damper.
- ❗ Follow the specified dimensions, specifications, and alignment of the cabinet. Warping, tilting or twisting of the cabinet or door may cause failure.
- ❗ This product is a part for architectural fittings. After installation, please check the function and safety of the final product. Please inform the end user how to use the product safely.
- ❗ Make sure to check the screws for slack at regular intervals (one month from first usage, half a year, and then one time every year is recommended).


INSTALLATION DRAWING (EXAMPLE)**CUT OUT DRAWING FOR DOOR AND DOORFRAME**

INSTALLATION PROCEDURE

1 Disassembly of Hinge




2 Installing Hinge to Door and Door frame



Caution
 Before installing base frame into doorframe, check that it is oriented correctly. If the orientation is incorrect, the door cannot be installed.

3 Hanging Door



- [1] Insert each hinge body (door side) deep into the base frame.
- [2] Hang the hinge body on the base frame. (Provisional holding state)

Caution
 Do not move the door at this stage as it may fall off.


- [3] While supporting the door, quickly tighten and secure the up and down adjustment screws to the position shown on the left.

VIDEO LINK



ADJUSTING DOOR POSITION

The arrows should point in the direction of adjustment when the door is closed.



①—⑤ is the order of adjustment. Please put a supporting spacer under the door when adjusting it. There are two adjustment screws on one hinge.

Vertical adjustment

- ① Loosen the adjusting screw one turn.
- ② Lifted the door to the correct height.
- ③ Finally, secure the adjusting screw.


Horizontal adjustment

- ④ Rotate the adjustment screw to the correct position.

Depth adjustment

- ⑤ Loosen the adjusting screw one turn and secure it in the optimum position.

Attaching the Screw Cover



Caution

- Do not remove the depth adjustment screw. The door may fall and cause injury.
- When adjusting the horizontal position, turn the two screws a little, by the same amount. The hinge may be broken if you keep turning one screw only. If you turn the adjustment screw to the right beyond the adjustment range, the parts will protrude, and the cover won't fit, and if you turn it further, the door will come off.

SUGATSUNE KOGYO CO., LTD.
 Tokyo, JAPAN

Phone: +81 3 3866 2260
 E-mail: export@sugatsune.co.jp

SUGATSUNE KOGYO (UK) LIMITED
 Reading, UK

Phone: +44 1189 272 955
 E-mail: sales@sugatsune.co.uk

SUGATSUNE EUROPE GmbH
 Düsseldorf, GERMANY

Phone: +49 211 53812 900
 E-mail: sales@sugatsune.eu

SUGATSUNE AMERICA, INC.
 California, USA

Phone: +1 310 329 6373
 E-mail: sales@sugatsune.com

Chicago, USA

Phone: +1 630 317 7072
 E-mail: sales@sugatsune.com

SUGATSUNE CANADA, INC.
 Montreal, CANADA

Phone: +1 514 312 5267
 E-mail: support@sugatsune.ca

SUGATSUNE SHANGHAI CO., LTD.
 Shanghai, CHINA

Phone: +86 21 3632 1858
 E-mail: lamp@sugatsune.com.cn

Guangzhou, CHINA

Phone: +86 20 6639 3554
 E-mail: lamp@sugatsune.com.cn

SUGATSUNE KOREA CO., LTD.
 Incheon, KOREA

Phone: +82 32 220 0603
 E-mail: sales@sugatsune-korea.co.kr

SUGATSUNE KOGYO INDIA PRIVATE LIMITED
 Mumbai, INDIA

Phone: +91 9867299597
 E-mail: sales@sugatsune.in

Delhi, INDIA

Phone: +91 9867299597
 +91 11 45093636
 E-mail: sales@sugatsune.in