#### AMP

# SOFT DOWN STAY NSDX-20 (R/L)K INSTALLATION INSTRUCTION




- Please read this instruction sheet carefully for proper installation and operation. Incorrect installation and improper use of the product may damage the unit or cause injury.
- This stay is designed for furniture or lightweight door and is equipped with a damping function.
- Sugatsune guarantees the quality of this product as for all its parts. It cannot however guarantee the final assembly as a whole.
- This product was manufactured and delivered with our utmost care. Should you however find any defect, please contact your dealer immediately.
- Sugarsune warrants that this product is free from defect for a period of one (1) year from the date of delivery.
- Sugatsune liability is limited to the replacement of this product by a similar one free of defect. In no case does this extend to the replacement of the installation or the cabinet as a whole.
- Please keep these instructions at hand for future use.
- Sugatsune cannot be held liable for any damage or injury caused by improper use or one different than the one this product was designed for.

### A CAUTIONS Any failure to observe the following precautions may result in personal injury or damage to the cabinet

- Make sure that installation position and specifications are followed. Unsuitable installation position may damage the mechanism when in case two stays are used together.
- Make sure that the arm of the stay is parallel with the side panel of the cabinet.
- Please avoid forced opening beyond the opening angle, and using excessive force while closing the door.
- This product is designed to operate at room temperatures between 0°C to 40°C (32F-104F).
- This product has a spring at the elbow section. Please be careful not to get your fingers caught in elbow section while you are handling the unit.
- 🜒 Performance of hardware will be affected by unique factors in each application. Hardware must be tested in intended application to confirm the function.
- lacktriangle It is necessary to periodically check the fixing screws for loosing. Tighten the loosed screws as required.
- Do not force the door to close faster. It can cause damage to the product or hinge(s)
- Please make sure to check the operation after installation.

#### ■ Model (For standard screw)

Item No.	Position	Suitable screw on stay	Suitable screw on mounting plate
NSDX-20LK	Left	φ3.5 × 3	φ3.5 × 3
NSDX-20RK	Right	φ3.5 × 3	φ3.5 × 3



#### APPLICABLE DOOR WEIGHT AND SIZE

This product must be applied to a door with specific weight and size. Lined Section on the right of the graph indicates applicable door weight range based on 1 unit per door.

Note-1: In case of 2 units (right & left) per door are used

Door Width can be twice as large, if the door height remains unchanged


Note-2: In case of different door thickness or specific gravity, door weight must fit with following formula

(1/2 door height [inch]  $\times$  door weight [lb] = 35  $\sim$  120 [lb·inch])

\*1 unit per door : MIN. ~ MAX. 1/2 door height [m]  $\times$  door weight [kg]  $\times$  9.8 = 1.96  $\sim$  6.86 [N·m] (20  $\sim$  70 [kgf·cm])  $(1/2 \text{ door height [inch]} \times \text{door weight [lb]} = 17 \sim 60 \text{ [lb·inch]})$ 

\*2 units (right & left) per door: MIN ~ MAX 1/2 door height [m]  $\times$  door weight [kg]  $\times$  9.8 = 3.92  $\sim$  13.72 [N·m] (40  $\sim$  140 [kgf·cm])

Above drawing shows for NSDX-20LK (left hand side mounting) and NSDX-20RK (Right hand side mounting) symmetrically.



Center of gravity (Density = 0.5)

\*In case of usual wooden flap of 20 mm thickness (specific gravity approx. 0.5)

### INSTALLATION PROCEDURE

- 1. Mount the body and arm fixing plate on sideboard and back of door with tapping screws (\$\phi 3.5\$) to oval holes temporarily.
- 2. Align notch on mounting plate and hole on arm by rotating the stays to fix them.
- 3. Check the function and adjust mounting plate on oval holes. Then fix them with the tapping screws in the round holes of the stay and mounting plate.
  - \*The side board must be strong enough for NSDX installation.

Mounting plates are available both in standard and clip type. When using a standard mounting plate type, be sure to fix it securely with supplied truss screw after installing the stay. When using a clip mounting plate type, be sure to insert arm completely.

#### **OPENNING ANGLE** OPENNING ANGLE SIDE BOARD 20 50 HINGE CENTER IN CASE OF CONCEALED HINGE CENTER IN CASE OF BUTT HINGE HINGE OR PIANO HINGE 23 83 73) 22

#### PIANO HINGE

78

В C D

125 100 126 101

97 72 103

### **CONCEALED HINGE**

In using a clip mounting plate type, be careful not to hit the arm or apply excessive force, as it may cause the arm to fall off and cause unexpected injury.
SPEED ADJUSTMENT

#### Upon completion of installation, make sure the door opens and closes properly. To adjust the opening/closing speed of door, turn speed adjustment screw.

In case 2 units (right & left) are used on a single door, the speed adjustment screws on both sides must be turned evenly.


STANDARD MOUNTING PLATE

70°

105



MOUNTING PLATE



#### **⚠** CAUTIONS

 $oldsymbol{\Delta}$  Cautions

- Do not turn the speed adjustment screw exceeding the limit.
- For speed adjustment, use a Philips (plus) screwdriver with \$\phi\$5 or less.

### SUGATSUNE KOGYO CO.,LTD

Tokyo, JAPAN Shanghai, CHINA
Phone: +81 (0)3 3866 2260 E-mail:export@sugatsune.co.jp Phone: +86 21 3632 1858

### SUGATSUNE KOGYO (UK) LTD **Reading, UK** Phone: +44 118 9272 955

E-mail:sales@sugatsune.co.uk

### **SUGATSUNE EUROPE GmbH** Düsseldorf, GERMANY Phone: +49 211 53812900

# SUGATSUNE SHANGHAI Co., LTD

E-mail:lamp@sugatsune.com.cn

### Guangzhou, CHINA

E-mail:lamp@sugatsune.com.cn

# SUGATSUNE KOGYO INDIA PRIVATE LIMITED

Mumbai, INDIA
Phone: +91 22 28314490/91 E-mail:sales@sugatsune.in

## SUGATSUNE AMERICA, INC

California, USA
Phone: +1 310 329 6373 E-mail:sales@sugatsune.com

#### Chicago, USA

Phone: +1 312 461 1081 E-mail:chicagoshowroom@sugatsune.com

#### SUGATSUNE CANADA, INC.

Phone: +1 514 312 5267 E-mail:support@sugatsune.ca

E-mail:sales@sugatsune.eu ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.