
LAMP. GS-GH5 Glass Pivot Hinge, GS-GB5 Glass Bracket Installation Manual

Thank you for selecting our product. Before starting installation, please read this manual thoroughly to ensure correct installation. Please keep this manual at hand for future reference.


ABOUT THE PRODUCT

- Inset hinge for a glass showcase.
- Door can be mounted with assembled hinges.
- Horizontal door position is adjustable when mounted.
- Vertical door position can be adjusted by adding a washer or a spacer.
- All hinges, brackets, and locks in the GS-series follow the same design pattern.



SPECIFICATIONS

Door size	W600 x H900
Door weight	Max. 8 kg
Glass	5 or 6 mm (Door)
thickness	8 mm (Top glass)



FOR YOUR SAFE WORK AND CORRECT INSTALLATION

Meaning of symbols







Caution If not followed injury or damage may result.


- Apply door stoppers to protect the hinges and glass door, when closing.
- Prepare a cabinet which can endure the weight of the door.
- ① Use tempered glass. It is recommended to use shatter-proof film on the glass. For areas where the glass brackets grip, make sure to remove the shatter-proof film before installing.




INSTALLATION DRAWING (EXAMPLE)

The images shown below are for a right opening door. A left opening door is the mirror opposite except with hinge A and B reversed on the left side.

[1] Wood Cabinet






DOOR AND CABINET PROCESS DIMENSIONS


(Right opening Shown. The left opening is a mirror image.)

Wood top board and Wood bottom board


 $\ensuremath{\,\%^{2}}$ Use hardwood or reinforce this part with adhesive to prevent the insert nut from loosening.




Glass door for wood top board




Tempered glass door for wood top board




Glass top board (for GS-GB5)





Glass door for glass top board







COMPONENT PARTS (PER BOX)











INSTALLATION Bracket GS-GB5

1 Assembling bracket parts



2 Door mount (See page3 3, to page4 5.)



SUGATSUNE KOGYO (UK) LTD

SUGATSUNE EUROPE GmbH

Düsseldorf, GERMANY
Phone: +49 211 53812900 E-mail:sales@sugatsune.eu

Guangzhou, CHINA Phone: +86 20 6639 3552 E-mail:lamp@sugatsune.com.cn

SUGATSUNE SHANGHAI Co., LTD

SUGATSUNE KOGYO INDIA PRIVATE LIMITED Mumbai, INDIA
Phone: +91 22 28314490/91 E-mail:sales@sugatsune.in

E-mail:lamp@sugatsune.com.cn

SUGATSUNE AMERICA, INC

California, USA
Phone: +1 310 329 6373 E-mail:sales@sugatsune.com

Chicago, USA

Phone: +1 312 461 1081 E-mail:chicagoshowroom@sugatsune.com.

SUGATSUNE CANADA, INC.

Phone: +1 514 312 5267 E-mail:support@sugatsune.ca

ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.