LAMP Pivot torque hinge HG-PTH30 Installation manual

ABOUT THE PRODUCT

- Use: Indoor rotary window, rotary panels for machinery.
- Range of use: Max. Weight: 10 kg, Window width: 350 500 mm, Height: 700 - 1200 mm, Thickness: 28 - 35 mm
- ■Operating temperature range: 0~40°C
- Feature: Enables rotary motion of window to allow airflow.
 - ·Torque hinge allows for easy adjustment of airflow.
 - ·Allows window to be guick released.
- Torque :3.0±20% N·m(30.6±20% kgf·cm)

FOR YOUR SAFE WORK, CORRECT INSTALLATION, AND SAFE USE

















- where it will be exposed to water
- O Do not use the hinge for a transom window which is exposed to strong winds.
- O Do not use lubricant on the hinges as it may damage them.
- This product is for indoor use only. Do not use outside or anywhere Be sure to use the retainer at the bottom. If you fail to fix the retainer, the window may fall.
 - ⚠ Install a door stopper since the hinge can rotate 360°
 - ⚠ Operating torque of the window may vary according to the room temperature or wind.


COMPONENT PARTS



(7) Countersunk head tapping screw 4x20...8 pcs



Detail F






INSTALLATION EXAMPLE t/2+ Close Open (9) Window height: H=(Frame height-12)±2 B=Frame height Note


Dimension (B-H) should be within 10 to 14 mm.

MOUNTING DIMENSIONS




INSTALLATION PROCEDURE


★ Determine the dimension so that the surface of the hinge will not protrude from the window.



[3] Incline the window, then insert it into the frame.



[4] Insert the shaft of the hinge $\ensuremath{ \bigcirc 2 }$ into the mounting plate $\ensuremath{ \bigcirc 1 }$ while holding the window inclined, then raise the



[5] Insert the hinge 3 into the mounting plate 4.

(6) With the arrow side facing up, insert the retainer §into the mounting plate4.

Hole for screw



Screw head should not protrude from the surface of (4)

firmly. If you fail to fix the retainer, the window may fall.

[7] Close the window, then check the left and right gaps between the frame and the window. If necessary, adjust the gaps

SUGATSUNE KOGYO CO., LTD.

Phone: +81 (0)3 3866 2260 E-mail:export@sugatsune.co.jp SUGATSUNE KOGYO (UK) LTD.

SUGATSUNE EUROPE GmbH Düsseldorf, GERMANY

Phone: +49 211 53812900 E-mail:sales@sugatsune.eu Phone: +91 9867299597

SUGATSUNE SHANGHAI Co., LTD. Shanghai, CHINA Phone: +86 21 3632 1858 E-mail:lamp@sug Guangzhou, CHINA Phone: +86 20 6639 3552 E-mail:lamp@sug F-mail:lamp@sugatsune.com.cn SUGATSUNE KOREA CO., LTD. Phone: +82 32 220 0603 E-mail:sales@

E-mail:lamp@sugatsune.com.cn

SUGATSUNE AMERICA, INC. California, USA Phone: +1 310 329 6373 E-mail:sales@sugatsune.com

Chicago, USA
Phone: +1 630 317 7072 E-mail:sales@sugatsune.com

2023.01 1245-2s

Reading, UK Phone: +44 118 9272 955

SUGATSUNE KOGYO INDIA PRIVATE LIMITED E-mail:sales@sugatsune.in

ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified