LAMP. ALT-2V-10 POCKET DOOR SYSTEM (OVERLAY) Installation Manual

Thank you for selecting our product. Before starting installation, please read this manual thoroughly to ensure correct installation. Please keep this manual at hand for future reference.

ABOUT THE PRODUCT

- · This product is a parts set for installation of a pocket door for cabinets.
- · The door is stored inside the cabinet.

FOR YOUR SAFE WORK AND CORRECT INSTALLATION

Meaning of symbols



Warning Caution



Prohibited



! Caution If not followed, injury or damage may result.

- Provide a cabinet that can withstand the weight and impact of opening and closing the door. Be sure to use the specified screws and tighten them securely. If the mounting strength is insufficient, the door may fall and cause injury.
- Follow the specified dimensions, specifications, and alignment of the cabinet. Warping, tilting or twisting of the cabinet or door may cause failure.
- Position the handle so that the hand holding the handle does not strike the side board.
- Make middle board removable for maintenance
- When moving the cabinet, remove the door and re-assemble it at the site.
- 1 This product is a part for furniture. After installation, please check the function and safety of the final product. Please inform the end user how to use the product safely.
- Make sure to check the screws for slack at regular intervals (one month from first usage, half year and then one time every year is recommended).
- **About door operation** · · · Inform cabinet users of the following precautions.
- \bigcirc Do not try to open the door more than 90°.
- Do not try to close the door before pulling out fully. It will damage the hinges.
- To prevent injuries, ensure that there is enough space around the handle.

COMPONENT PARTS


	1	2	3	4	(5)		F	arts s	et		
Item Name (Excluding last 2-digits)	Rail 16": AL127C-16 19": AL127C-19	<u></u>				(a) (b)	① ②	8	(G)		
	22" : AL127C-22 24" : AL127C-24 28" : AL127C-28	Connecting plate	Concealed hinge	Mounting plate	protector ALT-ADP	Catch AL127-CH	Roller DU-19-B4SBR	Roller bracket	Insert nut SC-107-13	Slider G-175	Stopper ALT-ADS
ALT - 2V - 10S [S type] Max Door Weight: 5 kg, Max Door Width: 560 mm, Door Height: 830-1060 mm, Max Door Thickness: 18-20 mm	2	ALT55-S : 1	2	2	2	1	2	A:1 B:1	2	2	2
ALT - 2V - 10M [M type] Max Door Weight: 6 kg, Max Door Width: 560 mm, Door Height: 1250 - 1500 mm, Max Door Thickness: 18-20 mm	3	ALT55-M : 1	3	3	3	2	2	A:1 B:1	2	2	3
ALT - 2V - 10L (L type) Max Door Weight: 8 kg, Max Door Width:: 560 mm, Door Height: 1650 - 1840 mm, Max Door Thickness: 18-20 mm	3	ALT55-L : 1	3	3	3	2	2	A:1 B:1	2	2	3
ALT - 2V - 10LL (LL type) Max Door Weight: 10 kg, Max Door Width: 600 mm, Door Height: 1990-2300 mm, Max Door Thickness: 18-20 mm	4	ALT55-LL : 1	4	4	3	2	2	A:1 B:1	2	2	3

	SCREWS AND TOOL SUPPLIED					
Item Name		13 Cross recessed bind head	14 Cross recessed raised countersunk	15)Low countersunk	16 Hexagon socket head	17 Hexagon socket
(Excluding last 2-digits)	tapping screw 3.5 × 15	tapping screw 4 × 16	head tapping screw 3.5 × 15	head screw M4 × 8	flange screw M4×6	screw keys
ALT - 2V - 10S	20	6	4	2	6	1
ALT - 2V - 10M/L	30	6	6	3	9	1
ALT - 2V - 10LL	37	6	8	4	12	1



INSTALLATION DRAWING


Door: 10 mm overlay to side, Inset to top and bottom.




· This is a side mount bracket, designed to be used for applications where floor mounting is not possible.

- · The bracket is non-handed.
- · Can support thick doors since it is mounted to the roller on two places.


and process						
Item Name	Installation Position					
ALT - 2V5BR1	For Lower Right & Upper Left					
ALT - 2V5BR2	For Upper Right & Lower Left					



Dimensions when using Side mount bracket




The drawing below shows the case when mounting on the right side board.




INSTALLATION PROCEDURE

1 Fixing Roller and Slider

Fixing on top board and bottom board



Fixing on side




®Slider

7)Rolle

Side mount bracket (Optional)


2 Fixing Mounting plate, Concealed hinge, Slider




3 Mounting Rail temporarily, Fixing Door stopper, protector

■Protector 5, Door stopper 11, Catch 6


Remove the original bumpers from the lower two rails (one for S type), and replace them with the catches. If the number of rails is two, replace it for the lower rail only.






Rail

Mount the rails in the specified position temporarily with two screws only. (Bind tapping screw 3.5 x 1.5) The rails will be fixed later.




4 Fixing Connection plate

Mount the connecting plate onto the rails temporarily.



5 Alignment of Rails

- (1) Hold the connecting plate and move it from the front end to the rear end, and align the rails so that the connecting plate moves smoothly.
- (2) Tighten the screws of the connecting plate, and check the movement again.
- (3) Tighten the screws on the rails, and check the movement.
- (4) If the movement is OK, fix the rails by fixing




6 Hanging door

- (1) Hold the door and mount concealed hinges on the mounting plates as shown.
- (2) Ensure that all of the screws are tightened firmly.

Push the button as shown

and remove the concealed

hinge.



Phone: +81 3 3866 2260

Reading, UK Phone: +44 1189 272 955 E-mail:sales@sugatsune.c

Phone: +49 211 53812 900 E-mail:sales@sugatsune.eu

SUGATSUNE KOGYO (UK) LIMITED


SUGATSUNE EUROPE GmbH

7 Adjusting door

How to adjust inclined door like the illustration below.

(1) Remove the door.


- (2) Loosen hexagon socket head screw (6)
- (3) Pushing the top of connecting plate ② to the rear, re-tighten the hexagon socket head screw 16.




Adjusting door position

Door front and rear, Vertical, Horizontal adjustment

If the door is tilted, adjust with the adjustment screws shown below.





∠!\ Caution |

·Do not use motor screwdrivers. ·Be careful not to overtighten the

SUGATSUNE KOGYO INDIA PRIVATE LIMITED Mumbai, INDIA Phone: +91 9867299597 E-mail:sales@sugatsune.in SUGATSUNE SHANGHAI CO., LTD. Shanghai, CHINA Phone: +86 21 3632 1858

Delhi. INDIA Phone: +91 9867299597 +91 11 45093636 E-mail:sales@sugatsune.ii

SUGATSUNE KOREA CO., LTD. Incheon, KOREA
Phone: +82 32 220 0603
E-mail:sales@sugatsune-korea.co.kr

SUGATSUNE AMERICA, INC. California, USA Phone: +1 310 329 6373

Chicago, USA Phone: +1 630 317 7072

SUGATSUNE CANADA, INC. Phone: +1 514 312 5267 E-mail:support@sugatsune.ca

Guangzhou, CHINA

Phone: +86 20 6639 3554