



Leveling ajustment screw

Front



Loosen both screws, adjust the door and retighten screws.



Leveling ajustment screw Back

SUGATSUNE EUROPE GmbH
Düsseldorf, GERMANY
Phone: +49 211 53812900
ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

SUGATSUNE KOGYO INDIA PRIVATE LIMITED
Mumbai, INDIA
Phone: +91 22 28314490/91
Phone: +91 22 28314490/91
E-mail:sales@sugatsune.in
ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

Guangzhou, CHINA


2019.08 0462-2

MonoFlat LIN-X hinge DesignTec.



MonoFlat LIN-X600 Instruction Manual

Thank you for purchasing this MonoFlat LIN-X hinge by SUGATSUNE. Before proceeding with the installation, please read this instruction manual carefully for the best possible result and ensure your safety.



WARNING

- Failure to observe the following precautions may result in injury and/or lead to damage to surrounding cabinets or fittings.
- Choose suitable screws to ensure of proper installation of the cabinet and door.
- Ensure that door size, weight and material correspond to the specifications stated in this manual.
- Do not disassemble or modify the system.


■ Product Specification


_				
Door width	550 ~ 650 mm			
Door height	600 ~ 900 mm			
Door thickness	15 ~ 24 mm			
Door weight	MAX 9 kg (per door)			

■ Parts List


① LIN-X body · · · · 2 p	CS.	② Mounting	plate ····	· 2 pcs.	③ Co	onnecting plat	te ····· 1 pc.
					L=540	0mm	
4 Connecting plate cover 2 pcs.	⑤ Cup cov	er ·····2pcs.	© Counters tapping	screw 3.5	t x15 ·· 6pcs.	7 Binding & ta screw 3.5x	apping 15 ····· 8pcs.
						E) annound (H) annound (H)	(E) Jaconson (E) Jaconson (E)








Installation position of mounting plate for cabinet side board




• Side overlay as shown in Fig.1 is:

19 mm for 230 Hinges mounting plate thickness : 0 mm (Standard) 14 mm for 230 Hinges mounting plate thickness : 5 mm





■ Installation


1 Mounting plate installation:



2 Cup cover installation:








Ensure that the two LIN-X bodies are parellel by measuring both the base and mounting plate distances.

4 Connecting plate installation: <u>Tighten</u> Hinge installation pitch 3Connecting Inser Connecting plate Connecting nut 4 Connecting plate cover

5 Door installation:



Ensure that the LIN-X body is securely attached to the mounting plates.