# LAMP SLUN-N SWING LIFT UP MECHANISM Design IEC LOGO DESIGN IEC




For proper installation and operation, we recommend that you read and follow these instructions carefully.


- Sugatsune cannot accept any claim for damages or injuries caused by improper use of this swing lift-up stay. Please refer to the "Model Selection" section below for the proper range of use.
- Sugatsune's liability is limited to the repair or replacement of a defective product. It shall in no way extend to the assembly as a whole.
- The utmost care was taken during the production of the SLUN-N. Should you however notice any defect, please notify your local dealer or Sugatsune (export@sugatsune.co.jp).

  The warranty period extends to one year from the shipping date.
- For improvement reasons, the content of this set may be changed without prior notice. We recommend that you check carefully the set content against the part list shown below and report any discrepancy to your local dealer before
- Operating temperature is 5~35°C. Function may vary depending on the temperature.
- Do not force the door open past its fully opened position.

①Distance plate 2pcs

- Do not use in excessively hot environment such as to hide an oven. Do not insert your hand or finger between the arms as this may lead to sever injury. Never attempt to open or disassemble the mechanism as this may lead to injury.
- Do not pull the arm down as it will spring back up violently and may cause serious injuries.





6 Holder 2pcs

®Countersunk tapping screw(3.5×20) 6pcs

Applicable door weight:

SLUN-3N 2.8~3.8 kg SLUN-4N 3.8~4.8 kg SLUN-5N 4.8~5.8 kg

Length of guide bar: I

Door size: Width (W<sub>1</sub>) 600, 900mm Height (H1) 390~450mm

**®Truss tapping screw** 

(4.5×12) 4pcs

Select the SLUN type according to the weight of the door (including

\*SLUB Bars are available in 4 standard sizes: 535, 835, 551 and 851mm.

SLUB bar needs to be cut depending on the cabinet width Wo and side panel thickness T.

Bar length L will depend on whether it is installed on Arm A or Arm B

Arm A installation: L= Wo-(Tx2)-35 Arm B installation: L= Wo- (Tx2) - 19

#### SUGATSUNE KOGYO CO.,LTD

⑤Damper 2pcs

Phone: +81 (0)3 3866 2260 E-mail:export@sugatsune.co.jp Phone: +86 21 3632 1858

SUGATSUNE KOGYO (UK) LTD

Reading, UK Phone: +44 118 9272 955 E-mail:sales@sugatsune.co.uk

# SUGATSUNE EUROPE GmbH Düsseldorf, GERMANY

Phone: +49 211 53812900 E-mail:sales@sugatsune.eu

### SUGATSUNE SHANGHAI Co., LTD

E-mail:lamp@sugatsune.com.cn

#### Guangzhou, CHINA

Phone: +86 20 6639 3552 E-mail:lamp@sugatsune.com.cn

#### SUGATSUNE KOGYO INDIA PRIVATE LIMITED SUGATSUNE CANADA, INC. Mumbai, INDIA

Phone: +1 514 312 5267 E-mail:support@sugatsune.ca Phone: +91 22 28314490/91 E-mail:sales@sugatsune.in

ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

# SUGATSUNE AMERICA, INC California, USA


Phone: +1 310 329 6373 E-mail:sales@sugatsune.com

#### Chicago, USA

Phone: +1 312 461 1081 E-mail:chicagoshowroom@sugatsune.com.

#### 2 Turn screw d left to bring the top of the door closer to the cabinet

2022 02 1018-2



## Installation

#### 1. Body installation:

(1) Draw a horizontal line at 354mm from the inside bottom of the cabinet.
(2) Line up the steel plate of the SLUN-N bodies ① and ② to the front of the cabinet and the line drawn in (1).

(3) Use screws 4 to secure both bodies to the cabinet.

# tapping screw (3.5×15) Fig. 4 (1) Install the mounting plates 3 to the back side of the door as per dimensions shown in Fig.3

4 Binding

Fig.5


#### 2. Door installation:

- (2) Line up both a screws of each mounting plates with the slots of the arms and slide the door down.

  \* Make sure that the screws are properly inserted in the slots before releasing the door.
- (3) Fasten both a screws securely.
- ⚠ Do not pull the arm down as it will spring back up violently and may cause serious injuries.

## 3. Bar installation:

- (1) Cut the bar to the necessary length as per instructions in the "Model Selection" section.
- (2) Install the bar to either arm A or arm B depending on the dimensions selected above. Arm A installation is recommended for wooden doors as bar is not visible in the open position. Arm B installation is recommended for glass door as bar is less visible in the closed position.



# screw(3.5×20) ⑥Holder Fig. 7 ⑦Distance plate

®Countersunk tapping

#### 4. Damper installation:

- (1) Line the distance plate ① and the holder ⑥ with the holes for the damper (Fig.7) and secure them with screws ®
- (2) Slide the damper 5 into the holder from the front side.

## Fig.9 Adjustment 1) Loosen both <u>a</u> screws Adjust height by turn b screw ③ Refasten both <u>a</u> screws securely 1) Loosen both c screws ② Adjust door position 3 Refasten both c screws securely d. 1) Loosen both a screws

3 Refasten both a screws securely




Fig.10


9SLUB

(A)

 Loosen both e screws on both sides ② Adjust height of the opened door

similarly on both sides.





**®Truss** tapping screw(4.5×12)



Spring strength adjustment:

Turn the screw at the back of stay body to adjust the spring strength.

