-AMP SOFT DOWN STAY NSDX-35 2S (with 2 stops at 65 / 90)



- Please read this instruction sheet carefully for proper installation and operation. Incorrect installation or use of this product may damage the unit or cause injury.
- This stay is designed for furniture or lightweight door and is equipped with a damping function.
- Sugatsune guarantees the quality of this product as for all its parts. It cannot however guarantee the final assembly as a whole. This product was manufactured and delivered with our utmost care. Should you however find any defect, please contact your dealer immediately.
- Sugatsune warrants that this product is free from defect for a period of one (1) year from the date of delivery.
- Sugatsune liability is limited to the replacement of this product by a similar one free of defect. In no case does this extend to the replacement of the installation or the cabinet as a whole.
- Please keep these instructions at hand for future use.
- Sugatsune cannot be held liable for any damage or injury caused by improper use or one different than the one this product was designed for.

$ilde{\mathbb{A}}$ <code>CAUTIONS</code> Any failure to observe the following precautions may result in personal injury or damage to the cabinet

- Make sure that installation position and specifications are followed. Unsuitable installation position may damage the mechanism when in case two stays are used together.
- Make sure that the arm of the stay is parallel with the side panel of the cabinet.
- Please avoid forced opening beyond the opening angle, and using excessive force while closing the door.
- This product is designed to operate at room temperatures between 0°C to 40°C (32F-104F).
- This product has a spring at the elbow section. Please be careful not to get your fingers caught in elbow section while you are handling the unit.
- Performance of hardware will be affected by unique factors in each application. Hardware must be tested in intended application to confirm the function.
- It is necessary to periodically check the fixing screws for loosing. Tighten the loosed screws as required.
- Do not force the door to close faster. It can cause damage to the product or hinge(s) .
- Please make sure to check the operation after installation.

■ Model (For standard screw)

Code No.	Position	Suitable screw on stay	Suitable screw on mounting plate
NSDX-35 2SL	Left	φ3.5 × 3	φ3.5 × 3
NSDX-35 2SR	Right	φ3.5 × 3	φ3.5 × 3

■ Model (For Euro screw)

Code No.	Position	Suitable screw on stay	Suitable screw on mounting plate
NSDX-35E 2SL	Left	φ6.2 × 2	φ3.5 × 3
NSDX-35E 2SR	Right	φ6.2 × 2	φ3.5 × 3

* \phi 6.2 Euro Screw to be applied

APPLICABLE DOOR WEIGHT AND SIZE

This product must be applied to a door with specific weight and size. Lined Section on the right of the graph indicates applicable door weight range based on 1 unit per door.


Note-1: In case of 2 units (right & left) per door are used Door Width can be twice as large, if the door height remains unchanged


Note-2: In case of different door thickness or specific gravity, door weight must fit with

following formula,

1/2 door height [m] \times door weight [kg] \times 9.8 = 1.96 - 4.9 [N \cdot m] (20 \sim 50 [kgf \cdot cm]) (1/2 door height [inch] \times door weight [lb]= 17 \sim 43 [lb · inch])

This item is same design as NSDX-35, and item no, NSDX-35 2S is stamped at the back side of body.





*In case of usual wooden flap of 20 mm thickness (specific gravity approx. 0.5)

*2 units (right & left) per door: MIN. - MAX. 1/2 door height [m] \times door weight [kg] \times 9.8 = 3.92 - 9.8 [N \cdot m] (40 \sim 100 [kgf \cdot cm]) (1/2 door height [inch] \times door weight [lb] = 35 \sim 85 [lb · inch])

Above drawing shows for NSDX-35 2SL (left hand side mounting) and NSDX-35 2SR (Right hand side mounting) symmetrically. Same mounting position is to be applied to the model of 35 EURO (type with EURO screw). Make a preparatory hole, Before drilling a φ6.2 EURO screw.

NSDX-35 2S INSTALLATION PROCEDURE

- 1. Mount the body and arm fixing plate on sideboard and back of door with tapping screws (\$\phi 3.5\$) to oval holes temporarily.
- 2. Align notch on mounting plate and hole on arm by rotating the stavs to fix them.
- 3. Check the function and adjust mounting plate on oval holes. Then fix them with the tapping screws in the round holes of the stay and mounting plate.

NSDX-35E 2S INSTALLATION PROCEDURE

- 1. Mount the stay on sideboard by applying EURO screw ($\phi 6.2$) to the larger round holes on the body.
- 2. Mount the arm fixing plate on back of door with tapping screws (\$\phi3.5) to the oval holes temporarily
- 3. Align notch on mounting plate and hole on arm by rotating the body to fix them.
- 4. Check the function and adjust mounting plate on oval holes. Then fix them with the tapping screws in the round holes of the body and mounting plate.
- *If the side board is not enough strength to support the stay, smaller round hole of the body must fix with tapping screw(\$\phi 3.5).

Mounting plates are available both in standard and clip type. When using a standard mounting plate type, be sure to fix it securely with supplied truss screw after installing the stay. When using a clip mounting plate type, be sure to insert arm completely.


In using a clip mounting plate type, be careful not to hit the arm or apply excessive force, as it may cause the arm to fall off and cause unexpected injury.

■CONCEALED HINGE


MEASURE- OPENING MENT ANGLE	Α	В	С
80° / 60°	106	105-S	121-S
90° / 65°	98	97 - S	113-S
100° / 70°	92.5	91.5-S	107.5-S


PIANO HINGE OR BATT HINGE

I Date Thirds on Date Thirds						
OPENING MENT ANGLE	Α	D	Е			
80° / 60°	100	99	115			
90° / 65°	91.5	90.5	106.5			
100° / 70°	85	84	100			



STANDARD MOUNTING **CLIP MOUNTING PLATE**





SPEED ADJUSTMENT SCREW

FASTER (SLOWER

SPEED ADJUSTMENT

Upon completion of installation, make sure the door opens and closes properly. To adjust the opening/closing speed of door, turn speed adjustment screw. In case 2 units (right & left) are used on a single door, the speed adjustment screws on both sides must be turned evenly.

⚠ CAUTIONS

Do not turn the speed adjustment screw exceeding the limit.

SUGATSUNE KOGYO (UK) LTD

Reading, UK
Phone: +44 118 9272 955 E-mail:sales@sugatsune.co.uk

SUGATSUNE EUROPE GmbH Düsseldorf, GERMANY
Phone: +49 211 53812900 E-mail:sales@sugatsune.eu

E-mail:lamp@sugatsune.com.cn

Guangzhou, CHINA Phone: +86 20 6639 3552

ISO9001(Japan Offices and Sugatsune America) and ISO14001(Chiba Production division and Logistics center), certified.

E-mail:lamp@sugatsune.com.cn

SUGATSUNE KOGYO INDIA PRIVATE LIMITED Mumbai, INDIA

Phone: +91 22 28314490/91 E-mail:sales@sugatsune.in

SUGATSUNE CANADA, INC.

SUGATSUNE AMERICA, INC California, USA

Chicago, USA

Phone: +1 514 312 5267 E-mail:support@sugatsune.ca

Phone: +1 310 329 6373 E-mail:sales@sugatsune.com

Phone: +1 312 461 1081 E-mail:chicagoshowroom@sugatsune.com