
LAMP HG-JH DAMPER HINGE INSTALLTION MANUAL




Thank you for selecting our product. Before starting installation, please read this manual thoroughly to ensure correct installation. Please keep this manual at hand for future reference.


APPLICABLE LID AND DOOR




APPLICATION EXAMPLES



DIMENSIONS





FOR YOUR SAFE WORK AND CORRECT INSTALLATION

Meaning of symbols








Caution If not followed, injury or damage may result.

- This product should be mounted on a surface which has enough strength to hold the moment of the lid. If not, the lid may fall and cause injury.
- O Do not use this product for applications outside of its specification.
- Use stays and stoppers with the dampers to prevent over rotation. If not the damper may be damaged.
- Align the axis of both hinges. If not, malfunction or damage will result.
- When mounting the hinges to an inclined surface, contact us.
- O Do not use excessive force as this may result in damage.
- ⚠ If the lid is released at a low angle, the damper may not work properly.
- ⚠ If the operating temperature increases, the door movement becomes quicker. If the temperature decreases, movement becomes slower. This is not a mechanical problem.
- The cap will loosen after several times of detachment.



COMPONENT PARTS



- Left hand or right hand are defined by the front view of the lid.
- •Screws (not provided): Hexagon socket head bolt 8 pcs, Plain washer (5 mm) 8 pcs

SPECIFICATIONS

Item name	Damper ※²			Torque **3
	Color	of shaft	Color of marking	N·m (kg · cm)
HG-JH25	White	Gray	Blue	3~5 (30.6~51)
HG-JH35	(for left)	(for right)	Red	5~7 (51~71.4)


¾² ... Left: Damper works when the shaft is turned anti-clockwise.

> Right: Damper works when the shaft is turned clockwise.

*3 ... The figure shows the torque of two hinges per lid.

Ambient temperature: 0° C~40° C Ambient humidity: Max. 90%

MAXIMUM LID TORQUE CALCLATION



 $T = m \times 9.8 \times L$

T:Maxim um lid torque (N·m)

m:Lid weight (kg)

D:Lid length(m)


A:Length of lid back from rotation center(m)


L:Distance from rotation center to lid center of gravity/(m)

L = D/2 - A

INSTALLATION


A. Assembly of brackets in alternative directions (Application example: lid (overlay)






- [1] Mount the lid bracket ② As shown in the left figure.
- [2] Assemble the cabinet bracket to the damper. (See left figure A or B.)
- (3) Fix the cabinet bracket to the cabinet together with the lid.
- [4] Verify that the lid movement is OK.
- [5] Put the four caps 4 onto the brackets.

B. Assembly of brackets in the same direction (Application example: lid (inset)





SUGATSUNE KOGYO (UK) LTD

SUGATSUNE EUROPE GmbH

E-mail:lamp@sugatsune.com.cn

Guangzhou, CHINA

E-mail:lamp@sugatsune.com.cn

SUGATSUNE AMERICA, INC

Phone: +1 310 329 6373 E-mail:sales@sugatsune.com Illinois, USA

Phone: +1 630 317 7072 E-mail:sales@sugatsune.com

SUGATSUNE CANADA, INC.

Phone: +1 514 312 5267 E-mail:support@sugatsune.ca